



A WORLD LEADER IN FUME EXTRACTION TECHNOLOGY



Dental accessories

Last Updated on 31.07.2018

Dust and fume extraction accessories for dental laboratory applications.

BOFA's DentalPRO range of dust and fume extraction systems and fume cabinets have been developed to effectively remove potentially harmful dust, particulates, fumes and vapours generated during dental laboratory manufacturing processes. BOFA offers a choice of interchangeable accessories designed to work with its DentalPRO series.

All BOFA dental accessories are specialist dust and fume capture devices, designed to cater for all dental laboratory applications, ideally suited to manual Monomer mixing and hand finishing applications, where they provide technicians with the flexibility to work without restriction, but in the knowledge that potentially harmful dust and fumes are being removed to maintain a safe working environment.

LED Light arm

- A portable device for maximum flexibility, but with a 'stay put' arm that maintains its position
- Contains a useful low cost LED light that illuminates detailed working areas

Plenum Funnel arm

- A portable device for maximum flexibility, but with a 'stay put' arm that maintains its position
- Designed to sit on the bench top at a particular angle that creates a laminar flow across the working area to capture the maximum level of dust and fumes

Down Draught Tray

- A portable device for maximum flexibility
- Specifically designed to capture fumes and vapours emitted by mixing Monomers

Bench Peg Assembly

- Designed to be attached to a bench top to capture the maximum amount of dust and fumes for close up work

Technology



ProTECT service plan



SureCHECK quality standard

Key features of the dental accessories

Rigid design Standard


Easy to use Standard

Contact BOFA at <https://bofainternational.com/en/contact/>
<https://bofainternational.com/en/portal/datasheets/dental-accessories/>




Technical specification

- 1. Flip top table mount
- 2. Stay Put arm
- 3. LED light ring
- 4. Plenum funnel
- 5. Down draught tray
- 6. Flexi hose 50mm
- 7. Cable for LED light arm
- 8. Bench peg assembly
- 9. Clear screen
- 10. Tabletop



Airflow drawing



Part numbers

Model	Part number
DentalPRO LED light arm - 50mm stay put arm	A1020314
DentalPRO down draught tray - 50mm flexi hose	A1020316
DentalPRO plenum funnel arm - 50mm stay put arm	A1020315
DentalPRO bench peg assembly	A375100

Hose kits

Model	Part number
Hose kit with fliptop table mount to connect to DentalPRO desk accessory	A1020309
Hose kit for the bench peg assembly	A1020110

Technical data

Description	Dimensions (HxWxD)	Construction	Approvals
LED light arm	630 x 50mm 24 x 2"	Formed plastic	CE
Plenum funnel arm	630 x 50mm 24 x 2"	Formed plastic	CE
Down draught tray	360 x 310mm 14.1 x 12.2"	Formed plastic	CE
Bench peg assembly		Powder coated metal	CE

Datasheet correct at time of publishing.

Where applicable, the carbon used in BOFA units is capable of removing a wide range of VOC's, however it is the responsibility of the user to ensure the carbon is suitable for their application. For specific applications, please contact us for details.

Think before you print! Please consider the environment before printing this document.

